


No.26 中間ソケット (Rc×G)



規 格	ネジD	ネジD1	L	L1	L2	六角 対辺
No.26×1/8	Rc1/8	G1/8	20	10	10	14
No.26×1/4	Rc1/4	G1/4	26	13	13	17
No.26×3/8	Rc3/8	G3/8	30	15	15	21
No.26×1/2	Rc1/2	G1/2	36	18	18	26
No.26×1/8×1/4	Rc1/8	G1/4	23	10	13	17
No.26×1/4×3/8	Rc1/4	G3/8	27	13	14	21
No.26×3/8×1/2	Rc3/8	G1/2	33	15	18	26
No.26×1/4×1/8	Rc1/4	G1/8	23	13	10	17
No.26×3/8×1/4	Rc3/8	G1/4	27	14	13	21
No.26×1/2×3/8	Rc1/2	G3/8	33	18	15	26

Gネジ側には、六角角径にV溝があります。