


No.27 中間ニップルソケット (R×G)



規 格	ネジD	ネジD1	L	L1	L2	六角 対辺
No.27×1/8	R1/8	G1/8	19	8	11	12
No.27×1/4	R1/4	G1/4	25	11	14	17
No.27×3/8	R3/8	G3/8	28	12	16	21
No.27×1/2	R1/2	G1/2	34	15	19	26
No.27×1/8×1/4	R1/8	G1/4	22	8	14	17
No.27×1/4×1/8	R1/4	G1/8	22	11	11	14
No.27×1/4×3/8	R1/4	G3/8	27	11	16	21
No.27×3/8×1/4	R3/8	G1/4	26	12	14	17
No.27×3/8×1/2	R3/8	G1/2	31	12	19	26
No.27×1/2×3/8	R1/2	G3/8	31	15	16	22

Gネジ側には、六角角径にV溝があります。