

# EA141AS-101-119

(オネジシステム)

	d	d1	D	L	L1	六角対辺
廃番 EA141AS-101	7	4	PT1/8	33	20	10
廃番 EA141AS-102	8.5	5	PT1/8	33	20	10
廃番 EA141AS-103	7	4	PT1/4	37	20	14
廃番 EA141AS-104	8.5	5	PT1/4	42	25	14
廃番 EA141AS-105	11	6	PT1/4	42	25	14
廃番 EA141AS-106	12.7	7.5	PT1/4	47.5	30	14
廃番 EA141AS-107	7	4	PT3/8	39	20	17
廃番 EA141AS-108	8.5	5	PT3/8	44	25	17
廃番 EA141AS-109	11	6	PT3/8	49	30	17
廃番 EA141AS-110	12.7	7.5	PT3/8	49	30	17
廃番 EA141AS-111	14.5	9	PT3/8	54	35	17
EA141AS-112	8.5	4.5	PT1/2	49	25	22
EA141AS-113	11	6	PT1/2	54	30	22
EA141AS-114	12.7	7.5	PT1/2	54	30	22
EA141AS-115	14.5	9.5	PT1/2	59	35	22
EA141AS-116	17.5	11.5	PT1/2	59	35	22
EA141AS-117	20.5	13	PT1/2	66	42	22
EA141AS-118	14.5	9.5	PT3/4	61	35	28
EA141AS-119	20.5	13	PT3/4	71	45	28

○ PTオスネジ×タケノコ径

(mm)

○ 材質 真鍮(クロームメッキ)

