


単位 mm

継手部品

■材質 黄銅棒C3604 ■表面处理 クロームメッキ

No.05 ニップル

(Rネジ×Gネジ)



規 格	ネジ D1	ネジD	L	d1	d	六角 対辺	EA品番
No.05 × 1/8	R1/8	G1/8	20	8	7	10	EA141AV-201
No.05 × 1/4	R1/4	G1/4	27	11	10	14	EA141AV-203
No.05 × 3/8	R3/8	G3/8	30	12	11	17	EA141AV-205
No.05 × 1/2	R1/2	G1/2	34	15	11	22	EA141AV-208
No.05 × 3/4	R3/4	G3/4	41	17	14	28	EA141AV-211
No.05 × 1/8 × 1/4	R1/8	G1/4	24	8	10	14	EA141AV-202
No.05 × 3/8 × 1/4	R3/8	G1/4	29	12	10	17	EA141AV-204
No.05 × 1/2 × 1/4	R1/2	G1/4	33	15	10	22	EA141AV-206
No.05 × 1/2 × 3/8	R1/2	G3/8	34	15	11	22	EA141AV-207
No.05 × 1/2 × 3/4	R1/2	G3/4	39	15	14	28	EA141AV-209
No.05 × 3/4 × 1/2	R3/4	G1/2	38	17	11	28	EA141AV-210