

LINCOLN

®

MODEL 1162 FULLY AUTOMATIC PNEUMATIC GREASE GUN

The variable speed trigger provides excellent grease flow control while the advanced pump design eliminates traditional priming issues

- Outstanding durability and dependability
- Fully automatic, continuous operation
- Variable-speed trigger
- Accessible check valve assembly
- Comfortable grip
- 30" high-pressure hose with coupler and attachment clip
- Includes a combination filler nipple and bleeder valve
- Superior flow performance obtained through advanced design



Pump Ratio:	40:1 at 150 psi
Max. Grease Pressure:	6,000 psi (414 bar)
Air Pressure Range:	40 - 150 psi (2.8 - 10.3 bar)
Weight:	5.375 lbs. (2.4 kg)

LINCOLN
®

Lincoln Industrial Corp.
One Lincoln Way
St. Louis, MO 63120-1578

Phone 314.679.4200
Fax 314.679.4359
www.lincolnindustrial.com

Form 444029 (9/07)
© Copyright 2007
Printed in U.S.A.