



◆N80M42(HRC65-67)以外はすべてハイス鋼(HRC62-64)です。

ブレード名称	型番	形状	使用範囲(mm)	刃先角度	重量(g)	EA品番	適用ホルダー
N80	BN8010		0 - 12	55°	35	EA207T-1	ダブルバー DB1000
N80M42	BN8043		0 - 12 (ステンレス鋼用)	55°	33	EA207T-2	
N80K	BN8110		2.4 - 11	55°	30	EA207W-1	Kホルダー EL04003
L3	BL3010		1 - 8	50°	19	EA207TB-1A	Lホルダー EL07013
	BL3001				6	—	
O-Ring	BO1010		1 - 3	40°	12	EA207WA-1	NG-1ハンドル NG1000
TC	BC1010		最小ねじ径 9	55°	12	EA207WB-1	