

(溶接火口)

	呼び	穴径
EA300BE-3	# 100	0.9mm
EA300BE-4	# 140	1.0mm
EA300BE-5	# 200	1.2mm
EA300BE-6	# 225	1.3mm
EA300BE-7	# 250	1.4mm
EA300BE-8	# 315	1.5mm
EA300BE-9	# 400	1.6mm
EA300BE-10	# 450	1.7mm



アセチレンガス用

ねじサイズ M8 × P1.0

材質 Bs BM (真鍮)

全長 36mm

六角対辺 11mm

(先端拡大)

