

(中型溶接火口)

| | 呼び | 穴径 |
|-------------|-------|-------|
| EA300B F-5 | # 200 | 1.2mm |
| EA300B F-6 | # 225 | 1.3mm |
| EA300B F-7 | # 250 | 1.4mm |
| EA300B F-8 | # 315 | 1.5mm |
| EA300B F-9 | # 400 | 1.6mm |
| EA300B F-10 | # 450 | 1.7mm |
| EA300BF-11 | # 500 | 1.8mm |
| EA300BF-12 | # 630 | 2.0mm |



アセチレンガス用

ねじサイズ M8 × P1.0

材質 Cu (銅)

全長 40mm

六角対辺 11mm

(先端拡大)

