

(中型SP火口 四割)

	呼び	穴径
EA300B J-5	# 200	1.2mm
EA300B J-6	# 225	1.3mm
EA300B J-7	# 250	1.4mm
EA300B J-8	# 315	1.5mm
EA300B J-9	#400	1.6mm
EA300B J-10	#450	1.7mm
EA300B J-11	#500	1.8mm
EA300B J-12	#630	2.0mm

**プロパン・天然ガス (13 A)用
四割**

ねじサイズ M8 × P1.0
材質 Bs BM+Cu (真鍮+銅)
全長 40mm
六角対辺 11mm



(先端拡大)

