

EA423RD-3-50 バックアップリング

◆ 寸法表
(単位: mm)

	バックアップ リング呼び番号	バイアスカット(テフロン)			適用Oリング JISB2401 呼び番号
		内径d	外径D	厚さT	
EA423RD-3	P 3	3	6	1.25±0.1	P 3
EA423RD-4	P 4	4	7		P 4
EA423RD-5	P 5	5	8		P 5
EA423RD-6	P 6	6	9		P 6
EA423RD-7	P 7	7+0.15 0	10 0 -0.15		P 7
EA423RD-8	P 8	8	11		P 8
EA423RD-9	P 9	9	12		P 9
EA423RD-10	P 10	10	13	P 10	
EA423RD-11	P 11	11	15	1.25±0.1	P 11
EA423RD-12	P 12	12	16		P 12
EA423RD-14	P 14	14+0.15	18 0		P 14
EA423RD-15	P 15	15 0	19 -0.15		P 15
EA423RD-16	P 16	16	20		P 16
EA423RD-18	P 18	18	22		P 18
EA423RD-20	P 20	20	24		P 20
EA423RD-21	P 21	21	25		P 21
EA423RD-22	P 22	22	26		P 22
EA423RD-24	P 24	24	30		1.25±0.1
EA423RD-25	P 25	25	31	P 25	
EA423RD-26	P 26	26	32	P 26	
EA423RD-28	P 28	28	34	P 28	
EA423RD-29	P 29	29	35	P 29	
EA423RD-30	P 30	30	36	P 30	
EA423RD-31	P 31	31	37	P 31	
EA423RD-32	P 32	32 0	38 -0.20	P 32	
EA423RD-34	P 34	34	40	P 34	
EA423RD-35	P 35	35	41	P 35	
EA423RD-36	P 36	36	42	P 36	
EA423RD-38	P 38	38	44	P 38	
EA423RD-39	P 39	39	45	P 39	
EA423RD-40	P 40	40	46	P 40	
EA423RD-41	P 41	41	47	P 41	
EA423RD-42	P 42	42	48	P 42	
EA423RD-44	P 44	44	50	P 44	
EA423RD-45	P 45	45	51	P 45	
EA423RD-46	P 46	46	52	P 46	
EA423RD-48	P 48	48	54	1.25±0.1	P 48
EA423RD-49	P 49	49	55 0		P 49
EA423RD-50	P 50	50	56 -0.20		P 50

