


EA425DA-41-104 ハーフユニオン



(Unit : mm)

型番 Part No.	適用チューブ外径T Applied Tube O.D.	接続ネジ Connecting thread	HEX	L	A	B	最小穴径 Minimum Opening
EA425DA-41	4	1/8	10	21	8	15	2.5
EA425DA-42	4	1/4	14	19.5	11	15	2.5
EA425DA-61	6	1/8	12	23	8	16.5	4
EA425DA-62	6	1/4	14	22.5	11	16.5	4
EA425DA-63	6	3/8	17	21	12	16.5	4
EA425DA-82	8	1/4	14	26.5	11	17.5	6
EA425DA-83	8	3/8	17	22	12	17.5	6
EA425DA-102	10	1/4	17	29.5	11	20	8
EA425DA-103	10	3/8	17	28.5	12	20	8
EA425DA-104	10	1/2	22	26.5	15	20	8

●使用流体 … 空気

●使用圧力 … 0~1MPa(10kgfcm²)

●使用温度 … -15~120°C(凍結なきこと)

●本体材質 … SUS316

●内部パッキン材質 … フッ素ゴム(バイトン)