


EA425DF - 4 - 10 パルクヘッドユニオン

(Unit : mm)



型番 Part No.	適用チューブ外径T Applied Tube O.D.	HEX	L	B	E	取付穴径 Panel Hole	最小穴径 Minimum Opening	M × P
EA425DF-4	4	14	31.5	15	4	13	2.5	M1.2 × 1.0
EA425DF-6	6	17	34.5	16.5	6	15	4	M14 × 1.0
EA425DF-8	8	19	37.5	17.5	9	17	6	M16 × 1.0
EA425DF-10	10	23	42.5	20	11.5	21	8	M20 × 1.0

— 線の
 商品は廃番商品です。