


# BU バルクヘッド ユニオン BULKHEAD UNION



T	TUBE	Part No.	A	B	C	D	E	F	W	Wx	G	PANEL MAX.
	mm											
3	1/8	<b>30- 3BU-C</b>	32	18	9	5	2	8	8	12	6.2	
4	—	<b>30- 4BU-C</b>	38	21	11	7	3	10	10	12	8.2	
6	1/4	<b>30- 6BU-C</b>	43	24	14	10	4	12	13	14	10.2	6
8	5/16	<b>30- 8BU-C</b>	51	28	18	12	6	17	17	19	14.2	
10	3/8	<b>30- 10BU-C</b>	60	32	21	16	8	22	22	23	17.2	
12	—	<b>30- 12BU-C</b>	70	37	25	18	10	26	24	26	20.2	
—	1/2	<b>30- 12.7BU-C</b>	70	37	25	18	10	26	24	26	20.2	
13	—	<b>30- 13BU-C</b>	70	37	25	18	10	26	24	26	20.2	

EA425HH-4  
EA425HH-6  
EA425HH-8  
EA425HH-10  
EA425HH-12

全ての寸法単位はミリメートルです。●Wは四角対辺の寸法です。●Part No.の斜体は非標準品です。

All dimensions are in millimeters. •W expresses the size of the opposite side of a square.

•Part numbers in italics indicate nonstandard items.