




Pipe Hangers & Supports

アカギのバンド

アカギ式

配管支持金具

御承認願図
WEB図面



サイズ	A	B	C	D	d	F	t	φ
15A	ø21.7	M6X20L	25	26	12.5	8.0	2.0	ø7.0
20A	ø27.2	"	"	"	"	"	"	"
25A	ø34.0	"	"	"	"	"	"	"
32A	ø42.7	"	"	"	"	"	"	"
40A	ø48.6	"	"	"	"	"	"	"
50A	ø60.5	M6X20L	25	26	12.5	8.0	2.0	ø7.0
65A	ø76.3	M8X25L	"	"	"	"	2.3	ø9.0
80A	ø89.1	"	"	"	"	"	"	"
90A	ø101.6	"	"	"	"	"	"	"
100A	ø114.3	"	"	"	"	"	"	"

No,1		No,2		No,3	
No,4		No,5		No,6	
品番 (No. OF PART) A10198	図面番号 (DRAWING No.) SAWA-415-4	3RD ANGLE PROJECTION			
品名 (NAME OF PART) ステン吊バンド	サイズ 15A~100A	尺度 (SCALE) 1:2(図は40A)			
材料 (MATERIAL) SUS304	製図 (DWG)	検図 (CHECKED)	承認図 (MGR)	作成年月日 (PRERAED) 平成13年4月23日	
表面処理 (FACE OF CORT)				配管支持金具の 株式会社 アカギ	