




# Pipe Hangers & Supports

アカギのバンド アカギ式 配管支持金具

御承認願図  
WEB図面



サイズ	A	B	C	H					L	P					S	t	T				
				T=20	T=25	T=30	T=40	T=50		T=20	T=25	T=30	T=40	T=50			20	25	30	40	50
15A	Φ21.7	M10	25	59	67	70	83	94	50	69	79	89	110	130	35	1.8	20	25	30	40	50
20A	Φ27.2	"	"	64	65	74	86	97	"	75	85	95	115	136	"	"	"	"	"	"	"
25A	Φ34.0	"	"	68	72	78	87	98	"	81	91	101	121	140	"	"	"	"	"	"	"
32A	Φ42.7	"	"	70	74	83	93	103	"	90	100	110	130	149	"	"	"	"	"	"	"
40A	Φ48.6	"	"	77	78	84	94	105	"	96	106	116	136	154	"	"	"	"	"	"	"
50A	Φ60.5	M10	25	78	87	90	100	110	50	108	118	128	148	166	35	1.8	20	25	30	40	50
65A	Φ76.3	"	32	88	94	98	108	117	"	123	133	143	163	181	"	"	"	"	"	"	"
80A	Φ89.1	"	"	95	101	106	116	127	"	135	145	155	175	195	"	"	"	"	"	"	"
100A	Φ114.3	"	"	—	112	118	128	138	"	—	171	181	201	221	"	"	"	—	"	"	"

No,1		No,2		No,3	
No,4		No,5		No,6	
品番 (No. OF PART) A10638	図面番号 (DRAWING No.) WATA-0799-1	三角法 3RD ANGLE PROJECTION			
品名 (NAME OF PART) ウレタンMSタイプ	サイズ 15A～100A×20T～50T	尺度 (SCALE) 1:4(図は40A×30T)			
材料 (MATERIAL) SPHC、硬質ウレタンフォーム	製図 (DWG) (CHECKED)	検査 (CHECKED)	承認図 (MGR)	作成年月日 (PRERAED) 平成28年1月5日	
表面処理 (FACE OF COAT) 電気亜鉛めつき仕上げ				配管支持金具の <b>アカギ</b> 株式会社 <b>アカギ</b>	