



Y311



Y312



Y313

Wire Hose Clamps

Wire Hose Clamps



The wire hose clamps are only used in low pressure applications, all parts are plated with Cr3⁺ Zinc coating under RoHS & REACH standard.

Y311 - Wire Hose Clamps with Hex Head Screw

Double Wires	Hex Head Screw	Bolt & Washer
Plated Carbon Steel	Plated Carbon Steel	Plated Carbon Steel

Y312 - Wire Hose Clamps with Flat Head

Double Wires	Flat Head	Bolt & Washer
Plated Carbon Steel	Plated Carbon Steel	Plated Carbon Steel

Y313 - Wire Hose Clamps with Grip Handle

Double Wires	Screw	Bolt & Washer	Grip Handle
Plated Carbon Steel	Plated Carbon Steel	Plated Carbon Steel	POM

	Clamping Range				Part Number		
	mm		inch		Hex Head Screw	Flat Head	Grip Handle
	Min.	Max.	Min.	Max.			
EA463AP-10,110	7	10	1/4	3/8	Y311-16D010	Y312-16D010	Y313-16D010
EA463AP-13,113	10	13	3/8	1/2	Y311-16D013	Y312-16D013	Y313-16D013
EA463AP-16,116	13	16	1/2	5/8	Y311-16D016	Y312-16D016	Y313-16D016
EA463AP-19,119	16	19	5/8	3/4	Y311-16D019	Y312-16D019	Y313-16D019
EA463AP-23,123	18	23	3/4	7/8	Y311-18D023	Y312-18D023	Y313-18D023
EA463AP-26,126	21	26	13/16	1	Y311-18D026	Y312-18D026	Y313-18D026
EA463AP-32,132	26	32	1	1-1/4	Y311-20D032	Y312-20D032	Y313-20D032
EA463AP-38,138	31	38	1-1/4	1-1/2	Y311-20D038	Y312-20D038	Y313-20D038
EA463AP-45,145	38	45	1-1/2	1-3/4	Y311-20D045	Y312-20D045	Y313-20D045
EA463AP-51,151	41	51	1-5/8	2	Y311-23D051	Y312-23D051	Y313-23D051
EA463AP-57,157	47	57	1-7/8	2-1/4	Y311-23D057	Y312-23D057	Y313-23D057
EA463AP-64,164	54	64	2-1/8	2-1/2	Y311-23D064	Y312-23D064	Y313-23D064
EA463AP-74,174	60	70	2-3/8	2-3/4	Y311-23D070	Y312-23D070	Y313-23D070
EA463AP-76,176	66	76	2-5/8	3	Y311-23D076	Y312-23D076	Y313-23D076
EA463AP-89,189	79	89	3-1/8	3-1/2	Y311-23D089	Y312-23D089	Y313-23D089
EA463AP-102,1102	92	102	3-5/8	4	Y311-23D102	Y312-23D102	Y313-23D102
EA463AP-103,1103	104	114	4-1/8	4-1/2	Y311-23D114	Y312-23D114	Y313-23D114
EA463AP-104,1104	117	127	4-5/8	5	Y311-23D127	Y312-23D127	Y313-23D127