

Hose Clamps

Standard Version (DIN 20039 A/B)

- Robust clamps made of malleable iron zinc plated and yellow passivated (free of chrome VI) or stainless steel 1.4401
- Robust, easy and secure hose assembly for various fittings and applications

Materials

- Clamps, spacers: Malleable iron zinc-plated and yellow passivated (free of chrome VI)/ Stainless Steel 1.4401
- Screws: Steel zinc-plated/ Stainless Steel A4-70

| Max. Working Pressure | Norm |
|-----------------------|---------------|
| PN 16 / 25 bar | DIN 20039 A/B |

Hose Clamps made of malleable iron, two parts with overlapping cast-on-spacers

| Hose-o.D./ | | L | B | Screw size | ⊠ | Weight | Type No. |
|--------------|-------|----|----|------------|----|--------|----------|
| Version | Range | | | | | | |
| Hose i.D. 13 | 17-22 | 60 | 17 | M 8x30 | 10 | 95 | S 22 |

Hose Clamps DIN 20039 A made of stainless steel 1.4401, two parts with loose spacers

| Hose-o.D./ | | L | B | Screw size | ⊠ | Weight | Type No. |
|--------------|-------|----|----|------------|---|--------|-------------------|
| Version | Range | | | | | | |
| Hose i.D. 13 | 18-26 | 63 | 18 | M 8x30 | 5 | 140 | SLE 13 EA463G-326 |
| Hose i.D. 19 | 26-33 | 71 | 18 | M 8x30 | 5 | 160 | SLE 19 EA463G-333 |
| Hose i.D. 25 | 32-40 | 81 | 18 | M 10x35 | 5 | 210 | SLE 25 EA463G-340 |

Hose Clamps DIN 20039 A made of malleable iron, two parts with loose spacers

| Hose-o.D./ | | L | B | Screw size | ⊠ | Weight | Type No. |
|---------------|---------|-----|----|------------|----|--------|-------------------|
| Version | Range | | | | | | |
| Hose i.D. 13 | 22-29 | 63 | 18 | M 8x30 | 10 | 128 | SL 29* EA463G-29 |
| Hose i.D. 19 | 28-34 | 71 | 18 | M 8x30 | 10 | 134 | SL 34* EA463G-34 |
| Hose i.D. 25 | 32-40 | 81 | 18 | M 10x35 | 10 | 188 | SL 40* EA463G-40 |
| Hose i.D. 32 | 39-49 | 91 | 20 | M 10x35 | 10 | 244 | SL 49* EA463G-49 |
| Hose i.D. 38 | 48-60 | 108 | 24 | M 10x45 | 5 | 297 | SL 60* EA463G-60 |
| Hose i.D. 50 | 56-72 | 116 | 25 | M 10x50 | 5 | 340 | SL 72 |
| Hose i.D. 50 | 60-76 | 127 | 25 | M 10x50 | 5 | 405 | SL 76 EA463G-76 |
| Hose i.D. 63 | 77-94 | 146 | 30 | M 12x55 | 5 | 556 | SL 94 EA463G-94 |
| Hose i.D. 75 | 89-101 | 139 | 25 | M 12x110 | 1 | 665 | SL 400 |
| Hose i.D. 75 | 94-115 | 176 | 35 | M 12x65 | 1 | 739 | SL 115 EA463G-115 |
| Hose i.D. 89 | 113-127 | 170 | 27 | M 12x110 | 1 | 890 | SL 525 |
| Hose i.D. 89 | 115-145 | 198 | 38 | M 12x80 | 1 | 1046 | SL 145 EA463G-145 |
| Hose i.D. 100 | 127-140 | 178 | 28 | M 12x110 | 1 | 972 | SL 550 EA463G-140 |
| Hose i.D. 100 | 135-155 | 194 | 27 | M 12x110 | 1 | 984 | SL 600 EA463G-155 |
| Hose i.D. 125 | 155-175 | 217 | 30 | M 12x125 | 1 | 1130 | SL 675 EA463G-175 |
| Hose i.D. 150 | 175-195 | 244 | 30 | M 12x125 | 1 | 1445 | SL 769 EA463G-195 |
| Hose i.D. 175 | 210-225 | 280 | 35 | M 16x150 | 1 | 2163 | SL 875 EA463G-225 |
| Hose i.D. 200 | 227-250 | 312 | 35 | M 16x150 | 1 | 2610 | SL 988 EA463G-250 |

*according to DIN 20039 A

Hose Clamps DIN 20039 B made of malleable iron, two parts with loose spacers and safety claws***

| Hose-o.D./ | | L | B | Screw size | ⊠ | Weight | Type No. |
|--------------|--------|-----|----|------------|----|--------|------------------|
| Version | Range | | | | | | |
| Hose i.D. 13 | 22-29 | 63 | 18 | M 8x30 | 10 | 142 | SK 29 EA463G-429 |
| Hose 19x2 | | 63 | 18 | M 8x30 | 10 | 140 | SK 29 FL** |
| Hose i.D. 19 | 28-32 | 77 | 21 | M 10x35 | 10 | 220 | SK 34 EA463G-432 |
| Hose 25x2 | | 77 | 21 | M 10x35 | 10 | 220 | SK 34 FL** |
| Hose i.D. 25 | 35-42 | 90 | 22 | M 10x35 | 10 | 272 | SK 39 EA463G-442 |
| Hose i.D. 28 | 42-45 | 98 | 24 | M 10x35 | 5 | 340 | SK 44 EA463G-445 |
| Hose i.D. 35 | 45-53 | 108 | 25 | M 10x45 | 5 | 380 | SK 51 EA463G-453 |
| Hose i.D. 42 | 55-60 | 119 | 26 | M 10x45 | 1 | 416 | SK 60 EA463G-460 |
| Hose i.D. 50 | 60-73 | 132 | 30 | M 12x55 | 1 | 637 | SK 73 |
| Hose i.D. 75 | 86-102 | 160 | 28 | M 12x55 | 1 | 860 | SK 75 |

**for flat hose

***PN 25 bar

