

Return Valves and Check Foot Valves with Strainer

made of Brass

- Return valves shut off water flows in one direction. Check foot valves are return valves assembled with a strainer.
- Avoid draining of the suction line, after pump has been switched off
- Perfectly tight hold even with very low pressure through Nitril rubber sealing
- Hostaform wedge with double central slide

Materials:

- Body: Brass MS 58 plain
- Valve: Nylon
- Springs: Stainless steel
- Seals: Nitril

Max. Working Pressure	Temperature	Opening pressure	Thread	Media	
PN 16 bar	up to +100°C	approx 0.02 bar	ISO 228	Water	1

Return Valves with female thread

Thread connection	L	D	Weight	Type No.
G 1/4 f	45	28.5	105	RSV 14 EA465L-2
G 3/8 f	45	28.5	93	RSV 38 EA465L-3
G 1/2 f	47.5	30	100	RSV 12 EA465L-4
G 3/4 f	53	37	159	RSV 34 EA465L-6
G 1 f	59	44.5	239	RSV 10 EA465L-10
G 1 1/4 f	66	56	348	RSV 54* EA465L-12
G 1 1/2 f	71	62.5	450	RSV 15* EA465L-14
G 2 f	80	78.5	730	RSV 20* EA465L-20

