










EA500BV-100

EA500BV-150

EA500BV-220

EA500BV-300

EA500BV-380

Art.No.	EAN 4021176	 mm	 inch	 mm	 inch	 x	 mm	 mm	max. t	 max. Nm	 kg
201-0	026423	100	3 15/16	75	2 31/32	1	-	14	1,5	25	0.43
201-1	026591	150	5 29/32	85	3 11/32	1	-	17	5	75	0.86
201-2	026676	220	8 21/32	130	5 1/8	1	8	22	7	150	2.44
201-3	026751	300	11 13/16	260	10 1/4	2	-	27	10	250	5.28
201-4	026836	380	14 31/32	300	11 13/16	2	-	27	10	250	5.62