


Transport equipment

Product data sheet

Article no.: 12515 Panelled end platform cart



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. Platforms and 1 end made of antislip waterproof plywood boards (insert type of board). 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	1600
Width of usable platform (mm)	800
Height of loading platform (mm)	283
Total length (mm)	1755
Total width (mm)	800
Total height (mm)	283
Tyres	Elastic solid rubber blue grey
Wheel size (mm)	200 x 50
Weight (kg)	64
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976125152