



	<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>	<b>E</b>	<b>F</b>
EA526BC-100	115 mm	55 mm	25 mm	17 mm	30 mm	40 mm
EA526BC-150	170 mm	80 mm	28 mm	19 mm	48 mm	60 mm
EA526BC-200	215 mm	110 mm	30 mm	20 mm	65 mm	75 mm