

Clamp curves, angles and edges



Band clamp BAN700



Order-No.	Clamping range	Band w x d	Angle range			
		mm		kg	qty.	V3
BAN700	Up to 7 m	25 x 1	60°-180°	0.56	5	

- Even pressure on mitre joints
- Crank handle can be relocated for right and left-handed users
- Contains: 1 band clamp, 4 Vario corners



Angle clamp WS



Order-No.	Opening	Jaw height	Current passage max.			
	mm	mm	mm	kg	qty.	V3
WS3 EA526CA-11	2 x 55	30	30	1.00	10	
WS6 EA526CA-12	2 x 100	36	60	2.30	4	

- Automatic adjustment to variously sized workpieces
- Quick – clamp with a spindle
- Stable body
- For attaching with table clamp – available as an accessory



One-handed edge clamp EKT



Order-No.	Opening	Throat depth			
	mm	mm	kg	qty.	V3
EKT55	10-55	45	0.82	1	

- For rapid one-handed operation
- Low weight
- Opening up to 55 mm



Edge clamp Kantenfix KF



Order-No.	Opening	Throat depth			
	mm	mm	kg	qty.	V3
KF2	10-40	80	0.76	4	
KF4	10-80	110	1.58	4	

- For quick one-handed operation
- Widths up to 80 mm

YouTube

