

EA527BS-21～-37 ブラインドリベット

- 材質…傘：ステンレス
軸：ステンレス



- プラケース付
(ケースの色は選べません)

サイズ：

	D (mm)	H (mm)	L (mm)	A (mm)	締付可能 板厚G (mm)	引張強度 (KN)	剪断強度 (kN)	入数 (個)
EA527BS-21	3.2	3.3	6.0	6.4	1.6~3.2	3.00	2.25	100
EA527BS-22	3.2	3.3	7.6	6.4	3.2~4.8	3.00	2.25	100
EA527BS-23	3.2	3.3	9.2	6.4	4.8~6.4	3.00	2.25	100
EA527BS-24	3.2	3.3	10.8	6.4	6.4~8.0	3.00	2.25	100
EA527BS-25	3.2	3.3	12.3	6.4	8.0~9.5	3.00	2.25	100
EA527BS-26	4.0	4.1	6.6	8.0	0.5~3.2	4.50	3.50	75
EA527BS-27	4.0	4.1	8.2	8.0	3.2~4.8	4.50	3.50	75
EA527BS-28	4.0	4.1	9.8	8.0	4.8~6.4	4.50	3.50	75
EA527BS-29	4.0	4.1	11.4	8.0	6.4~8.0	4.50	3.50	75
EA527BS-30	4.0	4.1	12.9	8.0	8.0~9.5	4.50	3.50	75
EA527BS-31	4.0	4.1	16.1	8.0	9.5~12.7	4.50	3.50	75
EA527BS-32	4.8	4.9	8.7	9.6	3.2~4.8	6.50	5.30	50
EA527BS-33	4.8	4.9	10.3	9.6	4.8~6.4	6.50	5.30	50
EA527BS-34	4.8	4.9	11.9	9.6	6.4~8.0	6.50	5.30	50
EA527BS-35	4.8	4.9	13.5	9.6	8.0~9.5	6.50	5.30	50
EA527BS-36	4.8	4.9	16.7	9.6	9.5~12.7	6.50	5.30	30
EA527BS-37	4.8	4.9	19.9	9.6	12.7~15.9	6.50	5.30	30

廃番

