

EA527BS - 1 ~ 19 ブラインドリベット

材質...傘：アルミ

軸：スチール

プラケース付

(ケースの色は選べません。)



サイズ：

| | D (mm) | H (mm) | L (mm) | A (mm) | 締付可能 板厚 G (mm) | 引張強度 (kg) | 剪断強度 (kg) | 入り数 (個) |
|--------------|--------|--------|--------|--------|-------------------|--------------|--------------|------------|
| EA527BS - 1 | 2.4 | 2.5 | 5.5 | 4.8 | 0.5 ~ 3.2 | 0.70 | 0.45 | 100 |
| EA527BS - 2 | 2.4 | 2.5 | 8.8 | 4.8 | 3.2 ~ 4.8 | 0.70 | 0.45 | 100 |
| EA527BS - 3 | 3.2 | 3.3 | 6.0 | 6.4 | 1.6 ~ 3.2 | 1.40 | 0.95 | 100 |
| EA527BS - 4 | 3.2 | 3.3 | 7.6 | 6.4 | 3.2 ~ 4.8 | 1.40 | 0.95 | 100 |
| EA527BS - 5 | 3.2 | 3.3 | 9.2 | 6.4 | 4.8 ~ 6.4 | 1.40 | 0.95 | 100 |
| EA527BS - 6 | 3.2 | 3.3 | 10.8 | 6.4 | 6.4 ~ 8.0 | 1.40 | 0.95 | 100 |
| EA527BS - 7 | 3.2 | 3.3 | 12.3 | 6.4 | 8.0 ~ 9.5 | 1.40 | 0.95 | 100 |
| EA527BS - 8 | 4.0 | 4.1 | 6.6 | 8.0 | 0.5 ~ 3.2 | 2.25 | 1.45 | 75 |
| EA527BS - 9 | 4.0 | 4.1 | 8.2 | 8.0 | 3.2 ~ 4.8 | 2.25 | 1.45 | 75 |
| EA527BS - 10 | 4.0 | 4.1 | 9.8 | 8.0 | 4.8 ~ 6.4 | 2.25 | 1.45 | 75 |
| EA527BS - 11 | 4.0 | 4.1 | 11.4 | 8.0 | 6.4 ~ 8.0 | 2.25 | 1.45 | 75 |
| EA527BS - 12 | 4.0 | 4.1 | 12.9 | 8.0 | 8.0 ~ 9.5 | 2.25 | 1.45 | 75 |
| EA527BS - 13 | 4.0 | 4.1 | 16.1 | 8.0 | 9.5 ~ 12.7 | 2.25 | 1.45 | 75 |
| EA527BS - 14 | 4.8 | 4.9 | 8.7 | 9.6 | 3.2 ~ 4.8 | 3.15 | 2.05 | 50 |
| EA527BS - 15 | 4.8 | 4.9 | 10.3 | 9.6 | 4.8 ~ 6.4 | 3.15 | 2.05 | 50 |
| EA527BS - 16 | 4.8 | 4.9 | 11.9 | 9.6 | 6.4 ~ 8.0 | 3.15 | 2.05 | 50 |
| EA527BS - 17 | 4.8 | 4.9 | 13.5 | 9.6 | 8.0 ~ 9.5 | 3.15 | 2.05 | 50 |
| EA527BS - 18 | 4.8 | 4.9 | 16.7 | 9.6 | 9.5 ~ 12.7 | 3.15 | 2.05 | 30 |
| EA527BS - 19 | 4.8 | 4.9 | 19.9 | 9.6 | 12.7 ~ 15.9 | 3.15 | 2.05 | 30 |

