

**THREADED INSERT SETTING TOOLS & KITS**



**EA527NK**



**Threaded Insert Setting Tool**

Part No Description

**1 2743** This thin sheet setting tool has been designed to enable threaded nut inserts to be set easily by hand. Invaluable to maintenance engineers for on-the-spot repairs. Supplied in storage wallet complete with 4mm, 5mm, 6mm and 8mm nose bushes and mandrels  
**EA527NK**

**Threaded Insert Nose Bush / Mandrel Conversion Kit**

Part No.	Size	Qty	Part No.	Size	Qty
72CK211	6 UNC	10	72CK224	1/4 UNF	
72CK212	8 UNC	10	72CK231	3mm	
72CK213L	10 UNC	10	72CK232L	4mm	EA527NK-4B
72CK214L	1 1/4 UNC	10	72CK233L	5mm	EA527NK-5B
			72CK234	6mm	EA527NK-6B
			72CK235	8mm	EA527NK-8B

**Inserts**

Part No.	Size	Qty	Part No.	Size	Qty
EA527NK-4 724504	4mm	100	724505	5mm	100
EA527NK-6 724506	6mm	100	724508	8mm	100

**Threaded Insert Setting Tool Kit**

Part No Description

**2 2745** As the 2743 but supplied with additional 4mm, 5mm, 6mm and 8mm threaded nutserts. Housed in a compact tool box for easy storage

- Designed for the quick, manual insertion of permanent load bearing threads in materials from 0.20" to 0.128"
  - Simple set up and easy uniform stroke allows a nutsert to be set in thin sheet materials without causing surface damage
  - A comprehensive range of conversion kits and inserts are available
- Product Benefits**
- One side application
  - Flush mounting
  - Permanent thread
  - Moisture resistant
  - Cost effective
  - Strong
  - Rapid
  - Vibration resistant
  - Portable

**TSN® GRIP RANGE**

SIZE	MINIMUM	MAXIMUM
4mm	0.51mm (0.020")	1.27mm (0.050")
5mm	0.51mm (0.020")	1.27mm (0.050")
6mm	0.76mm (0.030")	1.68mm (0.066")
8mm	0.91mm (0.036")	3.25mm (0.128")

All TSN® are BS, ISO metric screw threads in the coarse pitch series. TSN® (thin sheet nutsert) is the registered trademark of AVDEL LTD.