

## THREADED INSERT SETTING TOOLS

### Threaded Insert Setting Tool

Part No Description

- 1 2743** EA527NK This thin sheet setting tool has been designed to enable threaded nut inserts to be set easily by hand. Invaluable to maintenance engineers for on-the-spot repairs. Supplied in storage wallet complete with 4mm, 5mm, 6mm and 8mm nose bushes and mandrels

### Threaded Insert Nose Bush / Mandrel Conversion Kit

Part No.	Size	Qty	Part No.	Size
72CK211	6 UNC	10	72CK224	1/4 UNF
72CK212	8 UNC	10	72CK231	3mm
72CK213L	10 UNC	10	72CK232L	4mm EA527NK-4B
72CK214L	1/4 UNC	10	72CK233L	5mm EA527NK-5B
			72CK234	6mm EA527NK-6B
			72CK235	8mm EA527NK-8B

### Inserts

Part No.	Size	Qty	Part No.	Size	Qty
EA527NK-4 724504	4mm	100	724505	5mm	100
EA527NK-5 724506	6mm	100	724508	8mm	100

- Designed for the quick, manual insertion of permanent load bearing threads in materials from 0.20" to 0.128"
- Simple set up and easy uniform stroke allows a nutsert to be set in thin sheet materials without causing surface damage
- A comprehensive range of conversion kits and inserts are available

### Product Benefits

- One side application
- Flush mounting
- Permanent thread
- Moisture resistant
- Cost effective
- Strong
- Rapid
- Vibration resistant
- Portable

## TSN® GRIP RANGE

SIZE	MINIMUM	MAXIMUM
4mm	0.51mm (0.020")	1.27mm (0.050")
5mm	0.51mm (0.020")	1.27mm (0.050")
6mm	0.76mm (0.030")	1.68mm (0.066")
8mm	0.91mm (0.036")	3.25mm (0.128")