

絶縁閉端接続子抱合範囲の変更

0.32mm 1.32mm

コネクター抱合範囲の変更

灰色(8個):変更なし

青色(8個):0.81mm 0.52mm

橙色(8個):1.32mm 0.52mm

黄色(6個):2.08mm 0.82mm

赤色(3個):3.33mm 2.08mm

## EA538ND 圧着端子セット

 <p><b>絶縁丸端子</b> 抱合範囲: 0.32 ~ 1.32 mm 入数: 50 個</p>	 <p><b>絶縁丸端子</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 個</p>	 <p><b>絶縁丸端子</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 個</p>	 <p><b>絶縁丸端子</b> 抱合範囲: 3.33 ~ 5.26 mm 入数: 25 個</p>	 <p><b>絶縁丸端子</b> 抱合範囲: 3.33 ~ 5.26 mm 入数: 25 個</p>	 <p><b>圧着ペンチ</b> 【適用範囲】 ●絶縁端子: 1.5・2.5・6.0 mm ●裸端子: 1.5・2.5・4.0 ~ 6.0 mm ●ワイヤーストリッパー: 0.75・1.0・1.5・2.5・4.0・6.0 mm ●平ノットカッター (ISO): M2.6・M3・M3.5・M4・M5 ●ワイヤーカッター付</p>	
 <p><b>絶縁 Y 端子 (2種)</b> 抱合範囲: 0.32 ~ 1.32 mm 1.32 ~ 2.08 mm 入数: 各 50 個</p>	 <p><b>絶縁 Y 端子</b> 抱合範囲: 3.33 ~ 5.26 mm 入数: 25 個</p>	 <p><b>絶縁差込型端子 (雄・雌)</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 組</p>	 <p><b>ソケット&amp;プラグ</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 組</p>	 <p><b>コネクター</b> 灰色(8個): 0.32 ~ 1.32 mm 青色(8個): 0.52 ~ 2.08 mm 橙色(8個): 0.52 ~ 2.08 mm 黄色(6個): 0.82 ~ 2.08 mm 赤色(3個): 2.08 ~ 5.26 mm 総入数: 33 個</p>		
 <p><b>差込型端子 (雄・雌)</b> 抱合範囲: 0.32 ~ 1.32 mm 入数: 50 組</p>	 <p><b>差込型端子 (雄・雌)</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 組</p>	 <p><b>差込型端子 (雄・雌)</b> 抱合範囲: 3.33 ~ 5.26 mm 入数: 50 組</p>	 <p><b>絶縁閉端接続子</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 個</p>	 <p><b>ケーブルクランプ</b> 適合径: 3.2・4.8・6.4 mm 総入数: 25 個</p>		
 <p><b>絶縁スリーブ</b> 抱合範囲: 0.32 ~ 1.32 mm 入数: 50 個</p>	 <p><b>絶縁スリーブ</b> 抱合範囲: 1.32 ~ 2.08 mm 入数: 50 個</p>	 <p><b>絶縁スリーブ</b> 抱合範囲: 3.33 ~ 5.26 mm 入数: 25 個</p>	 <p><b>クイックスプライス</b> 抱合範囲: 0.82 ~ 2.08 mm 入数: 15 個</p>	 <p><b>プロモット</b> 内径/外径: 3.2/7.5 mm・ 4.8/10.2 mm・6.4/12.6 mm・ 7.9/14.8 mm・9.5/14.4 mm 総入数: 50 個</p>		
						 <p><b>結束バンド</b> 4.8(W)×190(L) mm 入数: 25 本</p>