

BESSEY® Snips

Compound Leverage Snips



Simply better.

BESSEY® Industrial Snips offer tradesmen the advantage of choosing fine quality at a competitive price. Quality in cutting tools means a sharper cut and a cutting edge with a longer life.

EA544AB...D15-SET
EA544AB-2...D15S-BE
EA544AB-3...D15A-BE

- 100% Power, 75% of the size
- Extremely compact cutting head for great manoeuvrability cutting the narrowest radii
- Practical locking mechanism allows one to open & close with one hand and limits the maximum opening of the snip
- Compound leverage considerably reduces effort required, improving productivity while reducing hand fatigue
- For long continuous, straight and curved cuts

- High grade steel cutting blades - up to HRC 59
- Micro-serrations for slip proof cutting



NEW

Multi-use snip, compact aviation snip (D15A)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal) Gauge	Approx. Weight Pounds	
D15A-BE	7 3/16	13/16	18	0.44	
D15AL-BE	7 3/16	13/16	18	0.44	
D15S-BE	7 3/16	13/16	18	0.44	
D15-SET	Includes: 1 x D15S-BE, 1 x D15A-BE, 1 x D15AL-BE in a nylon pouch				



Aviation snips (D16)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal) Gauge	Approx. Weight Pounds	
D16S-BE	9 1/2	1 3/4	18	1.25	
D16L-BE	9 1/2	1 9/16	18	1.25	
D16-BE	9 1/2	1 9/16	18	1.25	
D16-SET	Includes: 1 x D16S-BE, 1 x D16L-BE, 1 x D16-BE in a nylon pouch				



BESSEY® Tools North America
1-800-828-1004 · Fax (519) 621-3442



<http://www.facebook.com/BesseyToolsNorthAmerica>



<http://www.youtube.com/user/BesseyTools>



<http://www.besseytools.com/>

28-02-2011-E

BESSEY® Snips

Compound Leverage Snips




Simply better.

- High grade steel cutting blades - HRC up to 61
- Micro-serrations for slip proof cutting
- Right or left cutting versions



- High grade steel cutting blades - HRC up to 61
- Optimized leverage ration - 25% less effort
- Compact cutter head
- Right or left cutting versions



- Case hardened, high-speed steel edges - HRC up to 59
- For long continuous, straight and curved cuts
- Available in right or left cutting versions



- High grade steel, extra long cutting blade designed for continuous cuts - HRC up to 59
- Angled cutter heads keeps hands free from work
- For long continuous straight and large radius cuts
- Available in left cutting version only



Special hard cutting snips (D29SS)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal)	Approx. Weight	
	Inches	Inches	Gauge	Pounds	
D29SS-BE	10 1/4	1 9/16	18	1.25	
D29SSL-BE	10 1/4	1 9/16	18	1.25	



Offset snips, optimized (D29ASS)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal)	Approx. Weight	
	Inches	Inches	Gauge	Pounds	
D29ASS-BE	10 1/4	1 5/16	18	1.25	
D29ASSL-BE	10 1/4	1 5/16	18	1.25	



Offset, extra hard, high tolerance (D27AH)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal)	Approx. Weight	
	Inches	Inches	Gauge	Pounds	
D27AH-BE	10 1/4	1 5/16	18	1.25	
D27AHL-BE	10 1/4	1 5/16	18	1.25	



Long-nose, multi-purpose (D22AL)

BESSEY® Product #	Overall Length	Blade Length	Cutting Capacity (Regular metal)	Approx. Weight	
	Inches	Inches	Gauge	Pounds	
D22AL-BE	11	2 1/2	18	1.25	

