


# H I T



参考

パイプ径	外径	外周長さ (約)
61n.	165.2	519
81n.	216.3	680
101n.	267.4	840
121n.	318.5	1001
141n.	355.6	1117
161n.	406.4	1277
181n.	457.2	1436
201n.	508	1596

参考図

EA品番

EA546VD-1

EA546VD-2

EA546VD-3

EA546VD-4

EA546VD-5

EA546VD-6

EA546VD-7

EA546VD-8

記号 サイズ	組立					リンクプレート						ピン		
	L3	L4	総リンク数	全長 (L3+L4)	L4'	W	P	H	B	T	φd	φD	L1	L2
CW-3	4リンク	19リンク	23リンク	435.4	340.7	9.6	18.93	15±0.2	11.7	2.35	6.03 <sup>0</sup> <sub>-0.04</sub>	5.95	22	12.2
CW-3L	4 #	31 #	35 #	662.6	568	9.6	18.93	15 #	11.7	2.35	6.03 #	5.95	22	12.2
CW-4	4 #	23 #	27 #	511.1	416.5	9.6	18.93	15 #	11.7	2.35	6.03 #	5.95	22	12.2
CW-4L	4 #	49 #	53 #	1,003.3	908.6	9.6	18.93	15 #	11.7	2.35	6.03 #	5.95	22	12.2
CW-6	6 #	21 #	27 #	682.0	505.2	12.85	25.26	19.7±0.3	15.4	3.1	8.01 #	7.93	28	15.85
CW-6L	6 #	49 #	55 #	1,389.3	1,212.5	12.85	25.26	19.7±0.3	15.4	3.1	8.01 #	7.93	28	15.85
CW-8	6 #	21 #	27 #	853.2	632	16.2	31.60	24.8 #	19.3	3.9	9.61 #	9.53	35	20.8
CW-8L	6 #	49 #	55 #	1,738.0	1,516.8	16.2	31.60	24.8 #	19.3	3.9	9.61 #	9.53	35	20.8
CW-10	6 #	25 #	31 #	979.6	758.4	16.2	31.60	24.8 #	19.3	3.9	9.61 #	9.53	35	20.8
CW-10L	6 #	31 #	37 #	1,169.2	948	16.2	31.60	24.8 #	19.3	3.9	9.61 #	9.53	35	20.8
CWC-20	6 #	49 #	55 #	1,738	1,516.8	16.2	31.60	24.8 #	19.3	3.9	9.61 #	9.53	35	20.8
BW-200	4 #	11 #	15 #	945.8		32.4	63.05	50.2 #	39.2	7.9	20.02 #	19.84	70	40.4
BW-500	4 #	25 #	29 #	1,828.5		32.4	63.05	50.2 #	39.2	7.9	20.02 #	19.84	70	40.4
PIM 200	4 #	30 #	34 #	643.6		9.6	18.93	15±0.2	11.7	2.35	6.03 <sup>0</sup> <sub>-0.04</sub>	5.95	22	12.2
PIM 300	10 #	30 #	40 #	757.2		9.6	18.93	15±0.2	11.7	2.35	6.03 #	5.95	22	12.2
WV-6B	12 #	29 #	41 #	647.8		8.0	15.8	12.6	-	2.0	5.16	5.08	20	10.4

2009.10.09.作成