

Guarded Chisels

Hand guarded cold chisels fitted with strong guard designed to withstand the heaviest hammer blow and so protect the user's hand from injury.



Part No	Type	Length	Blade Width	Hexagon Dia.
22-410R/07	Grooving	250mm (10")	6.35mm (1/4")	15.9mm (5/8")
EA572H-19	Flat	205mm (8")	19mm (3/4")	15.9mm (5/8")
EA572H-25	Flat	250mm (10")	25.4mm (1")	22.2mm (7/8")
22-639R/07	Brick Cutting	230mm (9")	75mm (3")	19mm (3/4")
EA572J-100	Brick Cutting	230mm (9")	100mm (4")	25mm (1")
22-649R/07	Brick Cutting	230mm (9")	100mm (4")	25mm (1")
22-509R/07	Floorboard	230mm (9")	63.5mm (2 1/2")	17.5mm (11/16")