



<b>Order no.</b>	<b>SW [mm]</b>	<b>L1</b>	<b>B</b>	<b>L</b>	<b>L2</b>	<b>T</b>	<b>Weight [g]</b>
EA573A-3A	3	125	75	151	15	18	25
EA573A-4A	4	125	75	151	15	18	33
EA573A-5A	5	150	100	184	20	21	60
EA573A-6A	6	200	97	240	17	21	100