



(mm)

品番	サイズ	適合ネジ	軸径	A	B	重量(g)
EA573MD-4	T4	M1	2.5	45	13	2
EA573MD-5	T5	M1.6	2.5	48	14	2
EA573MD-6	T6	M2	2.5	52	15	2
EA573MD-7	T7	M2	2.5	56	16	2
EA573MD-8	T8	M2.5	2.5	60	17	3
EA573MD-9	T9	M2.5	3	63	17	4
EA573MD-10	T10	M3	3.5	67	18	6
EA573MD-15	T15	M3.5	3.5	72	20	7
EA573MD-20	T20	M4	4	77	21	9
EA573MD-25	T25	M5	5	83	22	15
EA573MD-27	T27	M5-6	6	90	23	21
EA573MD-30	T30	M5	6	98	25	23
EA573MD-40	T40	M8	7	107	27	35
EA573MD-45	T45	M8-10	8	117	29	69
<del>廃番</del> EA573MD-50	<del>T50</del>	<del>M10</del>	<del>10</del>	<del>128</del>	<del>32</del>	<del>80</del>
<del>廃番</del> EA573MD-55	<del>T55</del>	<del>M12</del>	<del>12</del>	<del>142</del>	<del>38</del>	<del>142</del>