

EA591HE - 1 ~ - 25 (タグ ブランク)

	サイズ(mm)	穴径	材質	厚さ
EA591HE - 1	16X48	3.2mm	アルミ	1mm
EA591HE - 2	16X71	4mm		
EA591HE - 3	19X79	4mm		
EA591HE - 5	25X54	3.2mm		
EA591HE - 11	16X48	3.2mm	真鍮	1mm
EA591HE - 12	16X71	4mm		
EA591HE - 13	19X79	4mm		
EA591HE - 14	19X46	3.2mm		
EA591HE - 25	25X54	3.2mm	ステンレス	0.8mm

形状

