

Product Datasheet

Product code: **F.SA.0**

Product type: High precision tweezers

Made in: Switzerland

Description: Type F high precision tweezers are suitable to delicate applications which require holding a flat component firmly while granting good visibility.

Tip description: straight, very fine, squared, strong, superior finish

Coating/finishing: Sandblasted

Body material: Anti-Magnetic Anti-Acid Stainless Steel (SA)


Picture:




Tweezer dimensions:

OAL	120.0 mm – 4.724 inch
Width	10.0 mm – 0.394 inch
Height	11.0 mm – 0.433 inch

Tip details:



Dimensions mm



Dimensions inch



Tip dimensions:

Tip width	1.70 mm – 0.067 inch
Tip thickness	0.07 mm – 0.003 inch