

**EA602AD-1~-23**  
(両口ラチェットレンチ)

- ソケット回転方向はワンタッチで転換
- 12ポイント
- ハンドル先端は鉄骨の穴あわせや、ワイヤロープの広げに最適な形状

※ ~~は取扱中止商品です。~~

<del>AD-1</del>	<del>サイズ</del>	<del>L</del>	<del>D</del>	<del>T</del>	<del>t1</del>	<del>t2</del>	<del>重量(g)</del>
<del>AD-1</del>	<del>10X12</del>	<del>225</del>	<del>30</del>	<del>36</del>	<del>11</del>	<del>10.5</del>	<del>220</del>
<del>AD-2</del>	<del>10X13</del>	<del>225</del>	<del>30</del>	<del>36</del>	<del>11</del>	<del>10.5</del>	<del>220</del>
<del>AD-3</del>	<del>11X13</del>	<del>225</del>	<del>30</del>	<del>36</del>	<del>11</del>	<del>10.5</del>	<del>190</del>
<del>AD-4</del>	<del>12X14</del>	<del>225</del>	<del>30</del>	<del>36</del>	<del>11</del>	<del>10.5</del>	<del>170</del>
<del>AD-5</del>	<del>13X17</del>	<del>270</del>	<del>36</del>	<del>45</del>	<del>14.5</del>	<del>14</del>	<del>330</del>
<del>AD-6</del>	<del>14X15</del>	<del>270</del>	<del>36</del>	<del>45</del>	<del>14.5</del>	<del>15.5</del>	<del>300</del>
<del>AD-7</del>	<del>14X17</del>	<del>270</del>	<del>36</del>	<del>45</del>	<del>14.5</del>	<del>15.5</del>	<del>300</del>
<del>AD-8</del>	<del>17X19</del>	<del>312</del>	<del>44</del>	<del>50</del>	<del>16</del>	<del>15.5</del>	<del>450</del>
<del>AD-9</del>	<del>17X21</del>	<del>312</del>	<del>44</del>	<del>50</del>	<del>16</del>	<del>15.5</del>	<del>450</del>
<del>AD-10</del>	<del>19X21</del>	<del>312</del>	<del>44</del>	<del>50</del>	<del>16</del>	<del>15.5</del>	<del>700</del>
<del>AD-11</del>	<del>19X22</del>	<del>312</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-12</del>	<del>21X24</del>	<del>355</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-13</del>	<del>21X26</del>	<del>355</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-14</del>	<del>22X24</del>	<del>355</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-15</del>	<del>23X26</del>	<del>355</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-16</del>	<del>24X27</del>	<del>355</del>	<del>50</del>	<del>55</del>	<del>17.5</del>	<del>17</del>	<del>700</del>
<del>AD-17</del>	<del>24X30</del>	<del>400</del>	<del>60</del>	<del>65</del>	<del>21.5</del>	<del>21</del>	<del>1050</del>
<del>AD-18</del>	<del>27X30</del>	<del>400</del>	<del>60</del>	<del>65</del>	<del>21.5</del>	<del>21</del>	<del>1100</del>
<del>AD-19</del>	<del>27X32</del>	<del>400</del>	<del>60</del>	<del>65</del>	<del>21.5</del>	<del>21</del>	<del>1080</del>
<del>AD-20</del>	<del>30X32</del>	<del>400</del>	<del>60</del>	<del>65</del>	<del>21.5</del>	<del>21</del>	<del>1080</del>
<del>AD-21</del>	<del>32X35</del>	<del>443</del>	<del>66</del>	<del>70</del>	<del>23</del>	<del>22.5</del>	<del>1500</del>
<del>AD-22</del>	<del>32X36</del>	<del>443</del>	<del>76</del>	<del>75</del>	<del>24.5</del>	<del>24</del>	<del>2120</del>
<del>AD-23</del>	<del>36X41</del>	<del>488</del>	<del>76</del>	<del>75</del>	<del>24.5</del>	<del>24</del>	<del>2140</del>

(単位mm)

