



RN4650

RN

■ 両口ラチェットレンチ

RATCHET WRENCH, Double Size

カチオン電着塗装 (防錆効果抜群)

▶ 特長

- 爪式は切換爪の窓が開口により砂かみの時は洗浄が簡単。
- 全サイズに安全ロープ取付穴を設けています。
(17×19・17×21・19×21は2ヶ所)

品番	呼び (mm)	サイズ(mm)						質量 (g)
		L	D	D1	D2	T	T1	
RN1012	10×12	225	28	18	15	14	11	160
RN1013	10×13	225	28	18	15	14	11	160
RN1014	10×14	225	28	19	15	14	11	160
RN1113	11×13	225	28	18	16	14	11	160
RN1214	12×14	225	28	19	18	14	11	160
RN1317	13×17	265	34	23	18	16	14.5	240
RN1319	13×19	310	41	26	18	18	16	400
RN1415	14×15	265	34	20	19	16	14.5	240
RN1417	14×17	265	34	23	19	16	14.5	240
RN1719	17×19	310	41	27	24	18	16	400
RN1721	17×21	310	41	29	24	18	16	400
RN1722	17×22	310	42	30	23	18	16	430
RN1921	19×21	310	41	29	27	18	16	400
RN1922	19×22	310	42	30	26	18	16	430
RN1924	19×24	355	49	33	26	20	18	680
RN2124	21×24	355	49	33	28	20	18	680
RN2126	21×26	355	49	36	28	20	18	680

EA602AT-1
EA602AT-2
EA602AT-3
EA602AT-4
EA602AT-5
EA602AT-6
EA602AT-7
EA602AT-8
EA602AT-9
EA602AT-10
EA602AT-11
EA602AT-12
EA602AT-13
EA602AT-14
EA602AT-15
EA602AT-16
EA602AT-17

品番	呼び (mm)	サイズ(mm)						質量 (g)
		L	D	D1	D2	T	T1	
RN2127	21×27	355	49	37	28	20	18	680
RN2224	22×24	355	49	33	30	20	18	680
RN2227	22×27	355	49	37	30	20	18	680
RN2326	23×26	355	49	36	31	20	18	680
RN2426	24×26	355	49	36	33	20	18	680
RN2427	24×27	355	49	37	33	20	18	680
RN2430	24×30	400	62	42	34	22	20.5	1,080
RN2632	26×32	400	62	44	36	22	20.5	1,080
RN2730	27×30	400	62	42	38	22	20.5	1,080
RN2732	27×32	400	62	44	38	22	20.5	1,080
RN3032	30×32	400	62	44	42	22	20.5	1,080
RN3235	32×35	445	67	47	43	24	21.5	1,400
RN3236	32×36	445	67	49	43	24	21.5	1,400
RN3541	35×41	490	76	55	47	26	24	2,050
RN3641	36×41	490	76	55	49	26	24	2,050
RN4146	41×46	500	83	61	55	29	23.5	2,500
RN4650	46×50	545	89	66	61	29	25.5	3,080

EA602AT-18
EA602AT-19
EA602AT-20
EA602AT-21
EA602AT-22
EA602AT-23
EA602AT-24
EA602AT-25
EA602AT-26
EA602AT-27
EA602AT-28
EA602AT-29
EA602AT-30
EA602AT-31
EA602AT-32
EA602AT-33
EA602AT-34