



Q

IF-9315C

93 mm - 15 Flutes

**⚠ WARNING! • Wear eye protection • Not for use with pneumatic or power tools
• Do not exceed 140 ft. - lbs. of torque**

¡ADVERTENCIA! • Use protección para ojos • No utilice con herramientas neumáticas o eléctricas • No exceda 140 pies por libra de torque

ADVERTISSEMENT! • Porter des lunettes de protection • Ne pas utiliser avec des outils pneumatiques ou électriques • Ne pas excéder 140 pieds-livres de couple de serrage

FOR THESE FILTERS • PARA ESTOS FILTROS • POUR CES FILTRES

AC DELCO	CASTROL (cont'd)	FRAM (cont'd)	FRAM (cont'd)	HASTINGS (cont'd)	NAPA (cont'd)	PENNZOIL	PUROLATOR (cont'd)	STP (cont'd)	WIX (cont'd)
PF2	CM8A	P3404	PH3985	LF391	1051	PZ-1	L30005/PER5	STP-24	51069
PF9	CM13	P3413	PH6606	LF732	1060	PZ-3	L30040/PER40	STP-25	51085
PF13	CM16	P3415	PH7328	154A	1061	PZ-7	L30119/PER119	STP-29	51182
PF20	CM30	P3594	PH8873	964F	1068	PZ-30	L30257/PER257	STP-228	51231
PF24	CM43	P3595	PH9100		1069	PZ-34	L34631/PER4631	STP-253	51250
PF25	CM3950	P3645	TG2	LEE	1085	PZ-42	L34875	STP-2801	51258
PF35		P3711	TG16	LF1HP	1182	PZ-45	L39001	STP-2815	51307
PF50	CHAMPION	P3726	TG30	LF2HP	1231		L40084/PER84	STP-2817	51319
PF932	C209	P3761	TG5	LF16HP	1258	PENSKE	L40316/PER316	STP-2820	51324
PF960		P3828	TG9100	LF17HP	1362	PN5		STP-2830	51362
PF963	CHRYSLER/ MOPAR	P6444	XG16	LF24HP	1372	PN8A		STP-2832	51372
PF970C	1851658	P6445	XG30	LF25HP	1380	PN13	RENAULT	STP-2850	51380
PF1180	3549957	P6485	XG5	LF29HP	1381	PN16	8933004195	STP-2856A	51381
PF1218	5281990	P6904	XG9100	LF42HP	1390	PN30		STP-2865	51390
PF1250	MDOO1445	P7075		LF75HP	1392	PN43	STP	STP-2872	51392
PF2191	MDOO5445	PH2	GM	LF78HP	1452	PN3531	S-01		51452
AMC	MDOO5450	PH5	25010908	LF253HP	1515	PN3950	S-01218	SUPERTECH	51515
8933004195	MDO30795	PH8A	250112760	LF820HP	1521	PORSCHE	S-016	ST2	51521
BOSCH		PH11	6435679	LF2801HP	1575	93010776400	S-024	ST5	51575
3320	FORD	PH13	6437462	LF2805HP	1839		S-025	ST8	51626
3321	C1AZ-6731A	PH16	6434946	LF2815HP		PUROLATOR	S-029	ST16	51839
3401	DIRY-6731A	PH25	6437994	LF2820HP		L10017/PER17	S-0228A	ST30	86122
3402	DPAZ-6731A	PH29	6438261	LF2830HP		L10018/PER18	S-0253	ST3950	89071
3410		PH30	6438384	LF2856HP		L10109/PER109	S-0256A		
3420	FRAM	PH37	94217272			L10193/PER193	S-0820	VOLVO	
3500	DG16	PH43		MOBIL-1		L10291/PER291	S-02801	1257492-7	
3510	DG2	PH2842		M1-109		L10343/PER343	S-02830	1266286	
CASITE	DG30	PH2844		M1-202		L14461/PER4461	S-02856	418432	
CF1A	DG5	PH2865A		M1-204		L14619/PER4619	S16	419719	
CF16	DG8	PH2921		M1-210		L14670/PER4670	S2	807180	
CF24	HM16	PH2975		M1-301		L15313	S25		
CF25	HM2	PH2977A		M1-302		L20033/PER33	S30	VW/AUDI	
CF25	P1101PL	PH3354		MOTOR- CRAFT		L20049/PER49	S3531	021115351A	
CF35	P1106	PH3381		FL-12A		L20081/PER81	S3569	068115561B	
CF321	P1119	PH3531		FL-842		L20253/PER253	S3950		
CF3651A	P1127	PH3569		NAPA		L20287/PER287	S3985		
	P1131	PH3651A		1049		L20290/PER290	S5	WIX	
	P1146	PH3776		1050		L22167/PER2167	S7328	51049	
CASTROL	P1147A	PH3791				L24651/PER4651	S8A	51050	
CM2	P3317	PH3950				L30001/PER1A	S8873	51051	
CM5		PH3963				L30003/PER3	STP-1	51061	
							STP-16	51068	



30333 Emerald Valley Pkwy.
Glenwillow, Ohio 44139 USA
www.imperial-tools.com
info@stridetool.com

Made in USA with US and globally sourced components. All Imperial products are designed, engineered and quality tested in the USA.

Producto hecho en Estados Unidos a base de componentes de EE.UU. y otras partes del mundo. El control de calidad y el diseño de todos los productos Imperial se lleva a cabo en EE.UU.

Fabriqué aux États-Unis à partir de composants en provenance des États-Unis et du monde entier. Tous les produits Imperial sont conçus et testés aux États-Unis.



©2009 Stride Tool Inc.

18288