

EA614C-6~34 サイズ

品番	S	D1	D2	L	T1	T2	g
EA614C-6	6	11	12	128	5.5	5	20
EA614C-7	7	12	14.4	134	5.8	5	21
EA614C-8	8	14	15.8	140	6.4	5.5	21
EA614C-9	9	15.1	18.9	150	6.5	4.6	31
EA614C-10	10	16.4	20.8	160	6	4.6	35
EA614C-11	11	18.2	22.4	166	6.3	4.6	40
EA614C-12	12	18.5	24.3	170	5	5.5	55
EA614C-13	13	20	27	178	7.8	6	65
EA614C-14	14	21	28.3	191	8.5	6	75
EA614C-15	15	22.4	30.4	197	9	6.7	92
EA614C-16	16	23.8	32.6	208	9.4	6	95
EA614C-17	17	26.8	35	225	10.8	7	145
EA614C-18	18	28	38.7	248	11	8.4	185
EA614C-19	19	28.5	39	248	11	8.4	185
EA614C-20	20	30.3	42.8	268	11.5	8.4	210
EA614C-21	21	30.8	43	270	12	9	235
EA614C-22	22	32.5	45	293	12.6	9	255
EA614C-23	23	34	49.3	317	13	9	340
EA614C-24	24	34	49.3	317	13.5	10	345
EA614C-25	25	36.4	52	335	14	10.7	410
EA614C-27	27	38.3	56.3	359	15.6	11.5	520
EA614C-28	28	43.5	62	405	16.3	11.5	600
EA614C-30	30	40.3	66.2	423	16.3	12.1	740
EA614C-32	32	46.6	63.2	427	16.1	13.1	790
EA614C-34	34	50	71	480	21.4	14.5	900

