


EA616GA-2~-20

(メガネレンチ)

○ クロム合金鋼

○ 12ポイント



	対辺	L	d1	d2	a1	a2	t	重量(g)
GA-2	6X7	165	10.5	11.8	6	7	18	46
GA-2B	7X8	180	11.8	13.1	7	7	20	60
GA-3	8X9	180	13.1	14.5	7	8	20	62
GA-3B	8X10	180	13.1	15.8	7	9	21	61
GA-4	10X11	200	15.8	17.2	9	9	23	93
GA-4B	10X12	220	15.8	19.2	9	10	25	131
GA-4C	10X13	220	15.8	20	9	10	25	122
GA-5	12X13	220	18.6	20	9	10	25	126
GA-6	12X14	220	20	21.3	9	10	25	134
GA-6A	13X15	245	20	22.6	10	12	27	163
GA-6B	13X16	245	20	23.9	10	11	27	164
GA-6C	13X17	245	20	25.3	10	12	27	169
GA-7	14X15	245	21.3	22.6	10	12	27	163
GA-8	14X17	245	21.3	25.3	10	12	27	165
GA-8A	16X17	255	23.9	25.3	11	12	27	181
GA-9	16X18	270	23.9	26.6	11	12	29	190
GA-10	17X19	270	25.3	28	12	13	29	220
GA-10A	18X19	275	26.6	28	12	13	29	228
GA-10B	18X21	300	26.6	30.7	12	13	31	279
GA-10C	19X22	300	28	32.1	13	14	31	315
GA-11	20X22	300	29.4	32.1	13	14	31	317
GA-12	21X23	315	30.7	33.4	13	14	31	312
GA-12A	21X24	330	30.7	34.7	13	14	34	384
GA-13	22X24	330	32.1	34.7	14	14	34	389
GA-14	24X26	330	34.7	37.3	14	15	34	427
GA-15	24X27	330	34.7	38.6	14	15	34	447
GA-16	25X28	350	36	40	14	15	34	414
GA-16A	27X30	360	38.3	42.6	15	15	37	595
GA-16B	27X32	360	39.3	47.2	15	16	37	596
GA-17	30X32	365	42.6	45.4	15	16	37	603
GA-17A	30X34	365	42.6	48	15	16	37	670
GA-18	34X36	400	48	51	16	17	38	750
GA-18A	36X41	440	53	60	17	18	40	1063
GA-19	41X46	485	60	68	18	19	42	1500
GA-20	46X50	535	65.2	73	19	20	45	1709

(単位mm)

— 線 = 廃盤商品