



EA616GE - 1 ~ - 12

(メガネレンチ)

クロム合金鋼
ストレートタイプ



	対辺	L	d1	d2	a	重量 (g)
GE - 1	6X7	100	9.6	11	4.5	14
GE - 2	8X9	115	12.5	14	5.5	19
GE - 2 B	8X10	115	12.5	15.4	6	18
GE - 3	10X11	130	15.4	16.6	6	28
GE - 4	12X13	150	18.2	19.5	6.5	42
GE - 4 A	13X16	170	19.5	24	7	54
GE - 4 B	13X17	170	19.5	25	8	57
GE - 5	14X15	165	21	22.5	7.5	55
GE - 5 B	16X17	170	23.8	25	8	68
GE - 6	16X18	185	23.8	26.3	8	59
GE - 7	17X19	185	25	27.6	8	78
GE - 7 A	18X19	185	26.3	27.6	9	84
GE - 7 B	19X22	210	27.6	32.4	9	109
GE - 8	20X22	210	29	32.4	9	109
GE - 9	21X24	235	30.5	34.7	10	128
GE - 10	24X27	290	34.7	38.5	11	225
GE - 10 A	27X32	320	38.5	45.5	12	283
GE - 11	30X32	325	43	45.5	12	289
GE - 12	30X34	325	43	48.5	12	307

廃盤

廃盤

(単位mm)