

EA616TA-1~-30
[チタン合金製]両口メガネレンチ



- 材質…チタン合金(6Al-4V)
- 非磁性、耐薬品性
- オフセット角度…40°

		(mm)			
	品番	メガネサイズ	メガネ厚み	全長	重量(g)
廃番	EA616TA-1	5×5.5	5	120	20
	EA616TA-2	6×7	5.5	145	30
	EA616TA-3	6×8	5.5	165	30
	EA616TA-4	8×9	6	165	30
廃番	EA616TA-5	8×10	6	165	30
	EA616TA-6	9×11	7	185	30
	EA616TA-7	10×11	7	185	30
	EA616TA-8	10×12	7	190	30
	EA616TA-9	11×13	8.5	205	40
	EA616TA-10	12×13	8.5	210	45
	EA616TA-11	12×14	8.5	210	50
	EA616TA-12	13×15	9	220	70
	EA616TA-13	14×15	9	220	80
	EA616TA-14	14×16	9	235	90
	EA616TA-15	14×17	9	235	100
	EA616TA-16	17×19	10.5	270	100
	EA616TA-17	18×19	10.5	270	100
	EA616TA-18	18×20	12	270	125
	EA616TA-19	19×22	12	305	150
廃番	EA616TA-20	20×22	12	305	150
	EA616TA-21	21×23	12.5	340	200
	EA616TA-22	22×24	12.5	340	250
廃番	EA616TA-23	24×27	14.5	385	300
	EA616TA-24	25×28	15	390	350
廃番	EA616TA-25	26×29	15.5	410	370
	EA616TA-26	27×30	15.5	410	400
廃番	EA616TA-27	30×32	19	420	450
	EA616TA-28	28×36	20	435	470
廃番	EA616TA-29	32×36	21	435	500
	EA616TA-30	41×46	22	450	600