

	サイズ	d1	d2	L	t1	t2	重量(g)
EA617XG-101	3/16"	7.6	11	50	41	4.2	15
EA617XG-102	7/32"	8.6	11	50	41	5	16
EA617XG-103	1/4"	9.6	11	50	41	5.5	19
EA617XG-104	9/32"	10.6	11	50	38.5	6.2	20
EA617XG-105	5/16"	11.6	11.6	50	38.5	6.7	24
EA617XG-106	11/32"	12.6	12.6	50	38.5	7.1	26
EA617XG-107	3/8"	13.6	13.6	50	38.5	7.9	33
EA617XG-108	7/16"	15.7	15.7	50	40.7	8.3	42
EA617XG-109	1/2"	17.3	17.3	50	40.2	9.2	44
EA617XG-110	9/16"	19.3	19.3	50	39.8	11.3	62

(1/4" ディープソケット)

(単位mm)

- 高張力合金鋼(HPQ)
- 差込角 1/4"

