

廃番
廃番

	サイズ	d1	d2	L	t1	t2	重量(g)
EA617XG-4	4	6.7	11	50	41	3.8	15
EA617XG-4.5	4.5	7.3	11	50	41	4.2	15
EA617XG-5	5	7.9	11	50	41	4.4	18
EA617XG-5.5	5.5	8.5	11	50	41	4.8	16
EA617XG-6	6	9.2	11	50	41	5.2	18
EA617XG-7	7	10.4	11	50	41	6	21
EA617XG-8	8	11.6	11.6	50	38.5	7.5	23
EA617XG-9	9	13	13	50	38.5	7.5	30
EA617XG-10	10	14.2	14.2	50	38.5	9	35
EA617XG-11	11	15.8	15.5	50	40.7	10.5	40
EA617XG-12	12	16.8	16.8	50	40.4	12	47
EA617XG-13	13	17.8	17.8	50	40.1	12	50
EA617XG-14	14	19	19	50	39.8	15	57

(1/4" ディープソケット)

(単位mm)

- 高張力合金鋼(HPQ)
- 差込角 1/4"

