

	サイズ	L1	L2	d	重量 (g)
EA617YL - 101	1/8"	52	20	17.8	40
EA617YL - 101B	9/64"	52	20	17.8	39
EA617YL - 102	5/32"	52	20	17.8	40
EA617YL - 103	3/16"	52	20	17.8	44
EA617YL - 104	7/32"	52	20	17.8	46
EA617YL - 105	1/4"	52	20	17.8	48
EA617YL - 106	5/16"	52	20	17.8	55
EA617YL - 107	3/8"	52	20	17.8	61

(3/8" インヘックスソケット)

クロム合金鋼
差込角 3/8"

