


	全長 (mm)	重量 (g)	A	B	C	D
EA618CB-1	50	103	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-2	75	144	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-3	125	194	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-4	150	250	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-5	250	358	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-6	300	450	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-7	400	655	φ 24.3mm	12.7mm	26mm	14.6mm
EA618CB-8	600	968	φ 24.3mm	12.7mm	26mm	14.6mm

(1/2" エキステンションバー)

○ 差込角 1/2"



←-----全長-----→

