


ソケット (6角)

最大径
6.35
mm
1/4



仕様

製品番号	二面幅寸法 (mm)S	寸法(mm) D1	寸法(mm) D2	寸法(mm) L1	寸法(mm) L	寸法(mm) d	質量(g)	EA品番
2S-03	3	6.0	13.0	3.0	21.0	2.0	7	EA618HK-3
2S-04	4	7.0	13.0	4.0	21.0	3.0	8	EA618HK-4
2S-4.5	4.5	7.0	13.0	4.0	21.0	3.5	8	EA618HK-4.5
2S-05	5	8.0	13.0	5.0	22.0	4.0	10	EA618HK-5
2S-5.5	5.5	8.5	13.0	5.0	22.0	4.0	10	EA618HK-5.5
2S-06	6	9.0	13.0	5.0	22.0	4.5	10	EA618HK-6
2S-07	7	11.0	13.0	6.0	22.0	5.0	20	EA618HK-7
2S-08	8	11.4	13.0	6.0	22.0	7.0	20	EA618HK-8
2S-09	9	13.5	13.0	6.0	22.0	7.0	20	EA618HK-9
2S-10	10	14.0	13.0	7.0	23.5	8.0	20	EA618HK-10
2S-11	11	15.0	13.0	7.0	23.5	9.0	20	EA618HK-11
2S-12	12	16.5	14.5	8.0	23.5	10.0	30	EA618HK-12
2S-13	13	18.0	16.0	10.0	23.5	10.0	30	EA618HK-13
2S-14	14	19.0	17.0	10.0	23.5	11.0	35	EA618HK-14

EA618HK-3



EA618HK-14

ご使用上の注意

- 注意** • インパクトレンチなど動力工具には使用しないでください。
/ Do not use with power tools.