

ディープソケット (6角)

 最大径
6.35
 mm
 1/4"


仕様

製品番号	二面幅寸法 (mm)S	寸法(mm) D1	寸法(mm) D2	寸法(mm) L1	寸法(mm) L	寸法(mm) d	質量(g)	EA品番
2S-03L	3	6.0	13.0	3.0	51.0	2.0	15	EA618HL-3
2S-04L	4	7.0	13.0	4.0	51.0	3.0	20	EA618HL-4
2S-05L	5	8.0	13.0	5.0	51.0	4.0	25	EA618HL-5
2S-06L	6	9.0	13.0	5.0	51.0	4.5	25	EA618HL-6
2S-07L	7	11.0	13.0	6.0	51.0	5.0	30	EA618HL-7
2S-08L	8	11.4	13.0	6.0	51.0	7.0	30	EA618HL-8
2S-09L	9	13.5	13.0	6.0	51.0	7.0	35	EA618HL-9
2S-10L	10	14.0	13.0	7.0	51.0	8.0	35	EA618HL-10
2S-11L	11	15.0	13.0	7.0	51.0	9.0	45	EA618HL-11
2S-12L	12	16.5	14.5	8.0	51.0	10.0	50	EA618HL-12
2S-13L	13	18.0	16.0	10.0	51.0	10.0	60	EA618HL-13
2S-14L	14	19.0	17.0	10.0	51.0	11.0	70	EA618HL-14



EA618HL-4



EA618HL-14

ご使用上の注意



注意 ・インパクトレンチなど動力工具には使用しないでください。
 / Do not use with power tools.