


ディーブソケット (12角)



仕様

製品番号	二面幅寸法 (mm)S	寸法(mm) L1	寸法(mm) D1	寸法(mm) D2	寸法(mm) L	寸法(mm) d	質量(g)	EA品番
3D-08L	8	6	11.7	17	54	7	35	EA618JF-8
3D-10L	10	8	14.7	17	54	8	50	EA618JF-10
3D-12L	12	9	18.0	17	54	10	60	EA618JF-12
3D-13L	13	9	19.0	17	54	10	70	EA618JF-13
3D-14L	14	10	20.0	18	54	11	80	EA618JF-14
3D-15L	15	10	21.0	19	54	11	100	EA618JF-15
3D-16L	16	11	22.0	20	54	14	110	EA618JF-16
3D-17L	17	11	24.0	20	54	14	120	EA618JF-17
3D-18L	18	13	25.0	21	54	15	145	EA618JF-18
3D-19L	19	13	26.0	21	54	16	160	EA618JF-19
3D-21L	21	15	29.0	23	64	18	175	EA618JF-21
3D-22L	22	15	30.0	24	64	18	195	EA618JF-22
3D-24L	24	17	32.0	26	64	20	200	EA618JF-24



ご使用上の注意

- ⚠ 注意** ・インパクトレンチなど動力工具には使用しないでください。
/ Do not use with power tools.