


ソケット (6角)



仕様

製品番号	二面幅寸法 (mm)S	寸法(mm)D1	寸法(mm)D2	寸法(mm)L1	寸法(mm)L	寸法(mm)d	質量(g)	
3S-5.5	5.5	8.8	17.0	4	26	4.0	20	EA618JK-5.5
3S-06	6	9.3	17.0	5	26	4.5	20	EA618JK-6
3S-07	7	10.7	17.0	5	26	5.0	20	EA618JK-7
3S-08	8	11.7	17.0	6	26	7.0	20	EA618JK-8
3S-09	9	13.2	17.0	6	26	7.0	25	EA618JK-9
3S-10	10	14.7	17.0	7	26	8.0	30	EA618JK-10
3S-11	11	15.7	17.0	8	26	9.0	30	EA618JK-11
3S-12	12	17.0	18.0	8	26	10.0	35	EA618JK-12
3S-13	13	18.5	18.0	9	27	10.0	35	EA618JK-13
3S-14	14	19.5	18.0	9	27	11.0	45	EA618JK-14
3S-15	15	21.0	18.0	10	29	11.0	50	EA618JK-15
3S-16	16	22.0	19.0	10	29	14.0	50	EA618JK-16
3S-17	17	23.0	19.0	11	30	14.0	70	EA618JK-17
3S-18	18	24.5	21.0	12	32	15.0	70	EA618JK-18
3S-19	19	26.0	21.0	13	32	16.0	75	EA618JK-19
3S-20	20	27.0	22.0	13	32	16.0	85	EA618JK-20
3S-21	21	28.0	22.5	13	32	18.0	95	EA618JK-21
3S-22	22	30.0	23.5	14	33	18.0	100	EA618JK-22
3S-23	23	31.0	25.5	14	33	20.0	110	EA618JK-23
3S-24	24	32.0	25.5	15	34	20.0	120	EA618JK-24