


ソケット (12 角)



仕様

製品番号	二重溝寸法(mm)S	寸法(mm)D1	寸法(mm)D2	寸法(mm)L1	寸法(mm)L	寸法(mm)d	質量(g)	EA品番
8D-27	27	40	46	19	60	22	380	EA618MK-27
8D-30	30	44	48	21	62	25	455	EA618MK-30
8D-32	32	50	50	21	62	25	600	EA618MK-32
8D-35	35	52	51	23	65	25	600	EA618MK-35
8D-36	36	54	51	24	65	30	600	EA618MK-36
8D-38	38	55	51	25	68	30	700	EA618MK-38
8D-41	41	60	51	27	70	35	800	EA618MK-41
8D-46	46	66	57	34	79	35	900	EA618MK-46
8D-50	50	72	57	35	82	38	1,000	EA618MK-50
8D-54	54	78	58	37	86	41	1,400	EA618MK-54
8D-55	55	80	58	37	86	41	1,400	EA618MK-55
8D-58	58	83	58	38	89	41	1,500	EA618MK-58
8D-60	60	85	58	40	91	—	1,600	EA618MK-60
8D-63	63	89	60	46	95	—	1,900	EA618MK-63
8D-65	65	90	60	46	95	—	1,800	EA618MK-65
8D-67	67	93	60	49	100	—	2,000	EA618MK-67
8D-70	70	97	60	51	105	—	2,200	EA618MK-70
8D-71	71	98	60	51	105	—	2,300	EA618MK-71
8D-75	75	103	65	53	110	—	2,700	EA618MK-75
8D-77	77	106	65	53	110	—	2,800	EA618MK-77
8D-80	80	110	65	56	115	—	3,100	EA618MK-80
8D-85	85	117	65	61	120	—	3,700	EA618MK-85
8D-90	90	120	70	63	125	—	3,870	EA618MK-90
8D-95	95	126	70	67	130	—	4,320	EA618MK-95
8D-100	100	132	70	71	135	—	4,660	EA618MK-100